


High performance series

## Micro annular gear pump mzr<sup>®</sup>-11507

For industrial production and process technology



- **High dosage precision**  
precision CV < 1% at low volumes
- **Long service life**  
wear-resistant tungsten carbide
- **Broad viscosity range**  
methanol, water, solvents, adhesives, grease, gel
- **High-power motor**  
AC-motor for use with external frequency inverter
- **Compact measurements**  
length 303 mm
- **High differential pressures**  
achievable even for low viscosity liquids
- **Pulseless delivery, low shear stress**  
rotary micro annular gear technology

The micro annular gear pump mzr-11507 is equipped with tungsten carbide rotors and bearings. Hard construction material and precision manufacturing techniques guarantee excellent dosage precision, high service life and wear resistance for low volume

dosage of non-lubricating liquids. Driven by a high-power three-phase AC-motor the pump has a compact design and covers the flow range from 29 ml/min to 1152 ml/min. The mzr-11507 is suitable for continuous delivery and discrete dosage of low and

high viscosity liquids. It achieves high differential pressures and provides a pulseless flow. Its robustness and the available accessories make it suitable for challenging applications.

### Applications

- Chemical processing
- Industrial and plant engineering
- Packaging
- Medical and pharmaceutical industry
- Mini plant technology
- Spraying
- Dispensing of adhesives
- Ink and paint dosage
- Vacuum applications

### Technical data

Flow rate	29 – 1152 ml/min
Smallest dosage volume	100 µl
Displacement volume	192 µl
Differential pressure range	0 – 60 bar (1 mPas); 0 – 150 bar (> 16 mPas)
Max. inlet pressure	10 bar (145 psi)
Ambient temperature range	-5 ... +40 °C
Liquid temperature range	-5 ... +60 °C (-20 ... +120 °C **)
Viscosity range	0,3 – 150.000 mPas
Precision	< 1 % Coefficient of Variation CV
Pulsation	6 %
Speed range	150 – 6000 U/min
Fluid connection	3/8" NPT internal thread, lateral optional 3/8" NPT internal thread, frontal
Wetted parts	stainless steel 316L (1.4435), tungsten carbide Ni-based; shaft seal: graphite-reinforced PTFE, alloy C276 (2.4819); static seals: FPM, optional: EPDM, FFPM
Motor	AC motor, IEC-Size 056, 4 poles, IP 55, rated voltage 240/400 V, rated frequency 100 Hz, 240 W
Temperature protection	thermal contact (NC)
Measurements (L x B x H)	303 x 110 x 171 mm
Weight	approx. 9 kg

Customized solutions on request.

\* for viscosity > 16 mPas

\*\* with optional heat insulation module, heating module


### Contact

HNP Mikrosysteme GmbH  
Juri-Gagarin-Ring 4 · D-19370 Parchim

phone +49| 3871| 451-301  
fax +49| 3871| 451-333



e-mail [info@hnp-mikrosysteme.de](mailto:info@hnp-mikrosysteme.de)  
<http://www.hnp-mikrosysteme.de>

## Measurements



Subject to technical changes.

## Flow charts



## Control (optional)



- frequency inverter S-FI-L1 for speed control for continuous dosage tasks
- nominal voltage 230 V AC
- power 250 W
- speed range 150 – 6000 U/min
- output frequency 0 – 240 Hz
- frequency resolution 1 Hz
- programmable analog input for speed set: 0-5 V, 0-10 V, 0-20 mA, 4-20 mA
- protective class IP 20
- internal radio interference suppression filter
- measurements (H x B x D): 146 x 93 x 83 mm

## Item number

10 03 01 39  
10 03 01 40  
66 04 01 04

Pump mzr-11507 S with three-phase AC-motor, lateral fluid connection 3/8" NPT  
Pump mzr-11507 F with three-phase AC-motor, frontal fluid connection 3/8" NPT  
frequency inverter S-FI-L1, 230 V AC, 250 W, IP 20, programmable analog input for speed set (0-5 V, 0-10 V, 0-20 mA, 4-20 mA)

## Accessories

*Liquid supply accessories*  
*Fluidic seal module*  
*Heat insulation module*  
*Heating module*

threaded fluid connectors, tubes, filters etc.  
use of liquids sensitive to air or water or for vacuum applications  
use for increased liquid temperature up to 120 °C  
active heating of the pump head up to 120 °C operating temperature

Micro annular gear pumps (and housings) are protected by assigned patents: DE 198 43 161 C2, EP 1115979 B1, US 6,520,757 B1, EP 852674 B1, US 6,179,596 B1, EP 1354135. Patents pending: DE 101 46 793, US 10,466,792, DE 10 2004 052 866. In the US, Europe and Japan additional patents are pending.  
mzr® is a registered German trademark of HNP Mikrosysteme GmbH.